



# WEIDMANN

### **Key Features**

- Temperature range: -200 °C to +300 °C
- · Electrically non-conductive
- Immunity to RFI, EMI, NMR and microwave radiation
- Resistance to high temperatures
- High accuracy
- Stable and repeatable measurements
- GaAs-based temperature sensor

### **Applications**

- Microwave and RF environments
- NMR analytical chemistry applications
- Food cooking and conditioning in microwave, Food pasteurization
- · Microwave assistes chemistry
- Pharmaceutical drying of powders, herbs and granulated mixtures



### DESCRIPTION

The fiber optic temperature probeTS3 stands for expanded flexibility with usual Weidmann quality and is the best choice for application in RFI, EMI, NMR and

Unlike the fiber optic sensorTS2, theTS3 comes with the possibility of a customizable length of the probe tip from 15 mm to 550 mm. Thanks to its fast response time of < 2 s and a tip diameter of 1.0 mm the TS3 temperature probe is small enough to fit in even the thinnest openings inside a measurement environment to deliver reliable data in real time.

All fiber optical temperature sensors can be connected to the fiber optic temperature measurement devices (FOTEMP), delivers accurate and complete reliable, stable and repeatable values. Starting at a light wave length of 850 nm GaAs (gallium arsenide) becomes optical translucent. Since the position of the band gap is temperature dependent, it shifts about 0.4 nm/K. Beyond that, Weidmann provides suitable extensions in different lengths without influencing the accuracy of the measurement result.

We are always anxious to adjust our offer to your special needs. In case of any further questions about individual measurement problems, lengths of sensors or connector types, please contact us.


microwave environments.

The fiber optic sensorTS3 allows exact temperature measurements within a range of -200 °C to +300 °C at an accuracy*2 of +/- 0.2 K.The jacket of the TS3 temperature probe consists completely of PTFE and ensures immunit to RFI, EMI, NMR and microwave radiation.

## TECHNICAL SPECIFICATION

Name of sensor	TS3
Measurement range *1	-200 °C to +300 °C
Inertia	Up to 12 K/s
Accuracy *2	+/- 0.2 K
Fiber Ø	200 um
Sensor standard lengths	2m up to 20m
Connector type	ST with metallic ferrule (-40 to 85 °C)
Signal conditioner	Compatible with all Weidmann fiber optic thermometers

### DIMENSION



- Long-term temperature range -200 °C up to +260 °C, short-term temperature range +260 °C up to +300 °C
- Statement only possible with analysis unit. See data sheet of the measurement device for information about technical data.

### DISCLAIMER - PLEASE READ CAREFULLY

DISCLAIMER – PLEASE READ CAREFULLY

This datasheet is based on Weidmann's knowledge as of the date of its publication. Instructions and explanations, while substantially accurate, are non-binding. Illustrations, specifications and average values are subject to change, do not guaranty actual product characteristics or specifications and are intended only to indicate possible uses of the Weidmann products. Customers alone must determine whether the products are suitable for their particular use and intended application and assume all risk and liability for unsafe or improper use or application. Weidmann shall not be liable for catalogue printing or other errors, for changes to Weidmann products or for any defects in the technical data or use of any information contained in the catalogue. Weidmann reserves the right always to revise the catalogue at any time, without notification. No part of this catalogue can form any part of or amend or alter any provision of any contract with respect to the Weidmann products. With respect to products in this catalogue, Weidmann disclaims all warranties, express or implied, including but not limited to, implied warranties of merchantability and fitness for a particular purpose. Weidmann shall not be liable for direct, indirect, special, incidental or consequential damages arising out of the purchase or use of products in this datasheet.

